


Gira System 55 enlarges the British Standard system to one of the largest available worldwide. All functions for intelligent building management can be integrated into it. This guarantees convenient, economical and secure living.

GIRA

Gira System 55

Installation system with greater options in design and functionality.



British Standard switch,
3-gang ON/OFF,
Gira Esprit, glass white



Surface-mounted home station video,
Gira Esprit, glass white



British Standard socket outlet,
1-gang, can be switched off,
with LED control light,
Gira Esprit, glass white

Gira System 55

The platform for a successful business

Gira is one of the leading brands in the field of intelligent building technology, and is a reliable partner to electricians, architects and planners. With System 55, Gira offers the ideal platform to individually and flexibly fulfil the needs of your customers.

The modular design enables a slim collection, while maintaining a wide range of programs and more attractive opportunities for variation. Inserts and frames in various colours, designs and materials are available for tailored mixing and matching to uniquely suit any property.

Whether simple, classic, or elegant, myriad décor concepts are possible thanks to the enormous number of combination options available for high-quality switch ranges and colours.

- High-quality materials: impact and shock-resistant material (thermoplastic)
- Homogeneous and easy-care surface, halogen-free and UV-resistant material, particularly resistant to signs of wear and tear.

Gira develops and produces systems and products which set standards both in technology and design. Gira products have already received a host of international design awards.




Gira System 55

Versatile installation methods

Installation in British Standard 80 mm wall box with support ring

Installation in EU round boxes



Gira Standard 55

Gira Esprit

Gira E2

Gira E3

Gira Event

Gira E22


Gira ClassiX

Gira System 55

The solution for all applications

Gira System 55 has over 320 functions for intelligent building technology, all of which can be installed in seven different switch ranges. It has been continuously developed since its introduction, and enhanced with new features and systems. Together, Gira's door communication and call systems constitute one of the largest selections of data connection technology worldwide, one which has also been integrated into the world of switches in terms of design and functionality.

All Gira System 55 central inserts and covers fit Gira Standard 55, E2, E3, Event, Esprit, ClassiX and E22 frames, as well as Gira Profile 55 and the modular function profile. It is possible to use an adaptor plate to ensure that all switches and functions can be used with British Standard wall boxes.



Gira British Standard installation system

Largest range, maximum diversity



Future-orientated technology and flexible solutions, combined with high-quality design: that's what intelligent building technology from Gira stands for. Automatic light control, time-dependent temperature control, distribution of music in all rooms, convenient door communication, integration of security systems and much more: the British Standard range from Gira is one of the largest available worldwide. The extensive assortment ranges from socket outlets, dimmers, rocker and push-switches to inserts for control of blinds, air-conditioning, door communication, the Gira KNX system and the eNet system.

All products of the British Standard core assortment comply with the inspection criteria for the "British Standard" from the Institute for Standardisation.

Individual selection and maximum functionality

- Award-winning design
- Adaptability to changing comfort and safety requirements for the different stages of life
- If required, upgrade investment can be staggered: for financial reasons owners start out with the Standard 55 frame, upgrading to a higher-quality frame, e.g. Gira Esprit, later on.






Installation in British Standard 80 mm wall box

The British Standard range from Gira complies with the inspection criteria for the "British Standard" from the Institute for Standardisation.

The range features 17 functions that can be integrated into the typically square British Standard box.

- Installation in British Standard wall box
- For single and double wall boxes only
- Gira switch ranges: E3, Event, Esprit, ClassiX, E22*















SQUARE "BRITISH STANDARD" BOX

Flush-mounted boxes	 1-gang	 2-gang			
Functions	 British Standard with 80 mm support ring (a total of 13 functions)	 British Standard with 80 mm support ring (a total of 4 functions)			
Switch ranges	 1-gang	 2-gang (no central bar)			
Usable frames	 E3	 Event	 Esprit	 E22*	 ClassiX

* British Standard frame

Gira British Standard installation system

80 mm plates for square wall box


Switch 3-gang, double 2 way	British Standard switch, 3-gang ON/OFF	British Standard switch, 3-gang, double 2-way	20 A switch
			
Universal rotary dimmer	Socket outlet 250 V/13 A, can be switched off, with LED control light	Touch dimmer	Socket outlet 250 V/15 A
			
2-gang socket outlet 250 V/13 A	2-gang socket outlet 250 V/13 A, can be switched off	20 A switch with LED control light	
			
Razor socket outlets for 2-gang frames without crossbar	2-gang socket outlet 250 V/13 A, can be switched off, with LED control light	Fused outlet with LED control light	
			

Frame design: pure white glossy, Gira Esprit, glass white

Installation in British Standard 80 mm wall box with support ring

A special 80 mm adaptor support ring is required for the installation of common System 55 functions in the square “British Standard” box.

















- Installation in “British Standard” wallbox with support ring
- Only for 1-gang devices
- Gira switch ranges: E3, Event, Esprit, ClassiX, E22*

SQUARE “BRITISH STANDARD” BOX	
Flush-mounted boxes	 1-gang box  Support ring
Functions	 System 55 with 71 mm support ring (a total of over 320 functions)
Switch ranges	 1-gang
Usable frames	 E3  Event  Esprit  E22*  ClassiX

* British Standard frame

80 mm plates for British Standard square wall box

Gira Standard 55 offers quality with a wide range of options for basic installation. It has more than 320 functions for convenient, safe and economical electrical installation and cover plates come in up to eight different colours.

 Push-button sensor 3 Plus, 2-gang	 Automatic control switch	 20 A switch with LED control light	 British Standard socket outlet 250 V/13A, can be switched off, with LED control light
 Hygrostat	 Electronic blind controller easy	 eNet radio switching/dimming top unit	 Universal/ISDN connection box
 eNet radio blind control button	 Transponder reader	 HomePlug AV network connection box	 Keyless In keypad
 Push-button sensor	 Electronic blind controller 2	 British Standard switch, 3-gang ON/OFF	 Automatic control switch 2

Frame design: pure white glossy, Gira Esprit, glass white

Installation in EU round boxes

Ranging from single-setting versions to 5-setting combinations – with more than 320 functions which can be adapted for installation into seven different switch ranges – Gira System 55 is extremely versatile. This fascinating design and functionality is also available on the UK market.

- Installation in EU round box:
- Ranging from single setting to 5 settings
 - Max. 4-setting frames with E22 and E22* for flat mounting, Esprit aluminium (in all four variants), chrome
 - Gira switch ranges: Standard 55, E2, E3, Event, E22*, Esprit, ClassiX, E22

Frame 1-gang
W 95 x H 95 x
D 9,85 mm



Frame 2-gang
W 166 x H 95 x
D 9,85 mm



Frame 2-gang
without central bar
W 166 x H 95 x
D 9,85 mm



Frame 3-gang
W 236,8 x H 95 x
D 9,85 mm



Frame 4-gang
W 308 x H 95 x
D 9,85 mm




Frame 5-gang
W 380,2 x H 95 x
D 9,85 mm



EU FLUSH-MOUNTED 71 MM ROUND BOXES


EU round boxes	 <p>1-gang</p>	 <p>Up to 5-gang</p>
Functions		
Switch ranges	 <p>1-gang to 5-gang including 2-gang frame without central bar</p>	
Usable frames	<div style="display: flex; justify-content: space-around; align-items: flex-start;"> <div style="text-align: center;">  <p>Standard 55</p> </div> <div style="text-align: center;">  <p>E2</p> </div> <div style="text-align: center;">  <p>E3</p> </div> <div style="text-align: center;">  <p>Event</p> </div> </div> <div style="display: flex; justify-content: space-around; align-items: flex-start; margin-top: 10px;"> <div style="text-align: center;">  <p>E22*</p> </div> <div style="text-align: center;">  <p>ClassiX</p> </div> <div style="text-align: center;">  <p>Esprit</p> </div> </div>	



* British Standard frame



British Standard safety razor socket outlet
Gira Esprit, glass C white



Gira hygrostat,
colour aluminium,
Gira Esprit, glass black



British Standard 2-gang socket outlet,
can be switched off,
with LED control light, anthracite
Gira Esprit, aluminium



British Standard switch,
3-gang ON/OFF, Gira Event Clear, sand

The platform for a successful business



Gira surface-mounted home station video, colour aluminium, Gira Esprit, aluminium black

Gira switch, 3-gang ON/OFF, colour aluminium, Gira Esprit, aluminium black

Gira flush-mounted radio, pure white glossy, Gira Esprit, glass C umber, control tower in black glass look , Gira docking station, pure white glossy, Gira socket outlet with hinged lid

Gira push switch, pure white glossy, Gira Esprit linoleum-plywood, blue



Gira push-switch/push-switch, pure white glossy, Gira Esprit linoleum-plywood, light grey

Gira switch ranges

Award-winning design and a multitude of functions

Gira Standard 55

- 01 Pure white glossy
- 02 Cream white glossy



Only for installation in round flush-mounted box.

Gira E2

- 03 Anthracite
- 04 Colour aluminium



- 05 Pure white glossy



Only for installation in round flush-mounted box.

Gira Event

- 06 Colour aluminium/anthracite



- 07 Anthracite/anthracite

- 08 Clear white/pure white glossy



- 09 Clear green/pure white glossy



- 10 Opaque mint/pure white glossy

- 11 Opaque blue/pure white glossy

Gira E3

- 18 Grey/beige Soft Touch/pure white glossy



- 19 Umbrage Soft Touch/anthracite

- 20 Blue/grey Soft Touch/anthracite



- 21 Grey-green soft touch/pure white glossy

- 22 Sand Soft Touch/pure white glossy




- 23 Light grey Soft Touch/pure white glossy

- 24 Grey Soft Touch/pure white glossy



- 25 Grey/beige Soft Touch/pure white glossy

- 26 Pure white glossy/pure white glossy



Gira Esprit Linoleum-Multiplex

- 12 Anthracite/pure white glossy




- 13 Light grey/pure white glossy

- 14 Dark brown/pure white glossy



- 15 Light brown/pure white glossy

- 16 Blue/pure white glossy




- 17 Red/pure white glossy

Gira Design Configurator

The entire Gira design system at a glance


Use the Gira Design Configurator to individually combine frame variants from the many Gira switch ranges with the various functions from the Gira product range.

For more information: www.gira.com/designconfigurator



Gira Esprit Metall

- 27 Aluminium black/colour aluminium




- 28 Aluminium brown/cream white glossy

- 29 Aluminium/anthracite



- 30 Aluminium bright gold/pure white glossy


- 31 Chrome/anthracite



- 32 Stainless steel/pure white glossy

Gira Esprit Glass

- 33 Glass black/colour aluminium



- 34 Glass amber/cream white glossy

- 35 Glass mint/colour aluminium



- 36 Glass white/pure white glossy

- 37 Glass C black/colour aluminium



- 38 Glass C amber/cream white glossy


- 39 Glass C mint/colour aluminium



- 40 Glass C white/pure white glossy


Gira ClassiX

- 41 Brass/pure white glossy




- 42 Bronze/pure white glossy

- 43 Brass black/pure white glossy




- 44 Bronze black/pure white glossy

- 45 Brass cream white/cream white glossy



- 46 Bronze cream white/cream white glossy

- 47 ClassiX art brass



- 48 ClassiX art bronze

Gira E22

- 49 Stainless steel



- 50 Aluminium

- 51 Thermoplastic/pure white glossy



Gira – the company

Made in Germany since 1905

Gira was founded in 1905 and is now a premium-quality manufacturer in the electrotechnical industry. Intelligent building technology from Gira stands for future-proof technology and flexible solutions, automatic light control, time-dependent temperature control, convenient door communication, integration of security systems and many other functions for more convenience, security and value. In Radevormwald, Germany, more than

1,200 employees produce switches and socket outlets as well as system components for intelligent building technology. Using Gira design platforms, new technologies are merged with the electrical installation to become part of the Gira switch system. Offering much more than just switches, the extensive range includes include communication connections and a flush-mounted radio as well as the Gira door communication system.



Aerial view of the Gira plant premises in Radevormwald, Germany.

Rooms flooded with light and open architecture in the production building.



Innovation, transparency, communication and design – the Gira production building symbolises the company’s philosophy.



www.catalogue.gira.com
The Gira online catalogue is clearly structured and illustrated throughout. It includes all the items of the Gira product range and enables simple creation of parts lists.



www.marking.gira.com
With the Gira Incription Service, you can professionally design call buttons for Gira door stations, LED signal lamps, orientation plates and push-button sensors.



www.designconfigurator.gira.com
Use the Gira Design Configurator to combine frame variants from Gira switch ranges with selected functions.



www.gira.com/download
Operating instructions, software, advertising materials and more are available in the download area.



www.giraacademy.co.uk
In addition to face-to-face seminars, the Gira Academy also offers online seminars and distance-learning courses.

All the UK face-to-face seminars and training sessions can be booked easily and conveniently. Places are always limited to ensure the best learning environment can be provided for all participants.



www.media.gira.com
The media database offers product illustrations, logos and videos to provide you with highquality images for your website and marketing activities.

GIRA

Gira
Giersiepen GmbH & Co. KG

Electrical installation systems
Dahlienstraße
42477 Radevormwald
Germany

+49(0)21 95 602 0
www.gira.com
info@gira.com

Gira UK Technical Hotline
00800 602 123

Gira UK Showroom
Gira Experience Centre
23-25 Baker Street
London
W1U 8EQ

