

#### Hand-held transmitter Mini

Order No.: 0412 00

## **Operating instructions**

## 1 Safety instructions

Electrical equipment may only be installed and fitted by electrically skilled persons.

Failure to observe the instructions may cause damage to the device and result in fire and other hazards.

Keep button cells out of reach of children! If button cells are swallowed, get medical help immediately.

Risk of explosion! Do not throw batteries into fire.

Risk of explosion! Do not recharge batteries.

These instructions are an integral part of the product, and must remain with the end customer.

## 2 Device components




Figure 1

- (1) Hand transmitter
- (2) Channel buttons
- (3) Key chain
- (4) LED

### 3 Function

#### **System information**

By statute, the transmitting power, the reception characteristics and the antenna cannot be changed.

The range of a radio system from the transmitter to the receiver depends on various circumstances.

The range of the system can be optimised by selecting the optimal installation location, taking into account the structural circumstances.

82531932 19.07.2016 **1/6** 




Figure 2: Reduced range due to structural obstacles

#### **Example of penetration of various materials:**

Material	Penetration
Wood, Plaster, Plasterboard	approx. 90%
Brick, Chipboard	approx. 70%
Reinforced concrete	approx. 30%
Metal, Metal grid	approx. 10%
Rain, Snow	approx. 1-40%

#### Intended use

- Radio hand transmitter for transmission of switching, dimming, and blind movement commands
- Operation in combination with suitable radio actuators

#### **Product characteristics**

- Two channels each with two buttons
- Battery-powered device

## 4 Operation

### Operating the transmitter

Each radio channel has two buttons. When a buttons is pressed, the red LED flashes. The radio transmitter has been taught.

- i In order to avoid faulty operation, never press more than one button at the same time.
- Press the desired button.
   Receiver responds depending on the button pressed and the length of the button-press.

Channel button	Length	Lighting	Venetian blind
left ∧	less than 1 second	Switch on	Slat adjustment
left ∧	longer than 1 second	Switch on/brighter	Blind moves up
right <b>V</b>	less than 1 second	Switch off	Slat adjustment
right <b>V</b>	longer than 1 second	Switch off/darker	Blind moves down

82531932 19.07.2016 **2/6** 



i The maximum transmitting length is 12 seconds, even if the channel button is pressed longer than 12 seconds.

## Change the battery

- Slacken screw on the rear of the enclosure of the hand-held transmitter and open enclosure (Figure 4).
- Remove empty battery.




Figure 3: Insert battery



#### WARNING!

Risk of chemical burns.

Batteries can burst and leak.

Replace batteries only with an identical or equivalent type.

- i Keep contacts of batteries and device free of grease.
- Insert new battery. Note the correct polarity (Figure 3).
- Close enclosure and tighten screw.
- Press any button for approx. 1 second.

The flashing LED indicates that the battery exchange was successful.

82531932 19.07.2016 3/6



# 5 Information for electrically skilled persons

# 5.1 Fitting and electrical connection

### Fitting the key chain




Figure 4: Slacken screw

 Slacken screw on the rear of the enclosure of the hand-held transmitter and open enclosure (Figure 4).




Figure 5: Fitting the key chain

- Carefully remove the semicircular predetermined breaking points (5) at the front of both enclosure sections.
- Place the ring of the key chain over the screw arbour.
- Close enclosure and tighten screw.

82531932 19.07.2016 4/6



# 5.2 Commissioning

#### Teach the channel of the radio transmitter.

In order for a receiver to understand a radio telegram of the radio transmitter, the receiver has to "learn" this radio telegram. A channel of the radio transmitter can be taught in any number of receivers. The teaching procedure only results in an assignment in the receiver.

When teaching a radio transmitter, the range of the receiver is reduced to about 5 m. The distance between the receiver and the transmitter being taught should therefore be between 0.5 m and 5 m.

- Switch radio receiver to programming mode (see instructions for radio receiver).
- Press the Λ- or V- button of the desired channel longer than 1 second.
   The LED of the receiver lights up as an acknowledgement of the teaching procedure.
- Exit programming mode of the receiver.
   The channel of the transmitter has now been taught in the radio receiver.

## 6 Appendix



Remove empty batteries immediately and dispose of in an environmentally friendly manner. Do not throw batteries into household waste. Consult your local authorities about environmentally friendly disposal. According to statutory provisions, the end consumer is obligated to return used batteries.

#### 6.1 Technical data

Rated voltage
Battery type
Radio frequency
Transmitting range in free field
Dimensions W×H×D
Ambient temperature
Relative humidity

DC 3 V 1×lithium CR 2032 433.05 MHz ... 434.79 MHz typ. 30 m 73×40×19 mm 0 ... +55 °C max. 80 % (No moisture condensation)

# 6.2 Troubleshooting

#### Receiver does not respond, or only sometimes.

Cause 1: battery in the transmitter is empty.

Change the battery.

Cause 2: Radio range exceeded. Structural obstacles reduce the range.

Decrease distance to radio receiver.

# **6.3 Conformity**

Gira Giersiepen GmbH & Co. KG hereby declares that the radio system type Order No. 0412 00

corresponds to the directive 2014/53/EU. You can find the full article number on the device. The complete text of the EU Declaration of Conformity is available under the Internet address: www.gira.de/konformitaet

# 6.4 Warranty

The warranty follows about the specialty store in between the legal framework as provided for by law

Please submit or send faulty devices postage paid together with an error description to your responsible salesperson (specialist trade/installation company/electrical specialist trade). They will forward the devices to the Gira Service Center.

82531932 19.07.2016 **5/6** 



Gira Giersiepen GmbH & Co. KG Elektro-Installations-Systeme

Industriegebiet Mermbach Dahlienstraße 42477 Radevormwald

Postfach 12 20 42461 Radevormwald

Deutschland

Tel +49(0)21 95 - 602-0 Fax +49(0)21 95 - 602-191

www.gira.de info@gira.de

82531932 19.07.2016 6/6