

Radio wall transmitter insert

Order No.: 0511 00

Operating instructions

1 Safety instructions

Electrical equipment may only be installed and fitted by electrically skilled persons.

Serious injuries, fire or property damage possible. Please read and follow manual fully.

Keep button cells out of reach of children! If button cells are swallowed, get medical help immediately.

Risk of explosion! Do not throw batteries into fire.

Risk of explosion! Do not recharge batteries.

The radio communication takes place via a non-exclusively available transmission path, and is therefore not suitable for safety-related applications, such as emergency stop and emergency call.

Do not shorten, extend or strip the antenna. Device can be damaged.

These instructions are an integral part of the product, and must remain with the end customer.

2 Device components




Figure 1

- (1) Transmitter
- (2) Battery compartment
- (3) Function switch
- (4) Connector strip

3 Function

System information

By statute, the transmitting power, the reception characteristics and the antenna cannot be changed.

The range of a radio system from the transmitter to the receiver depends on various circumstances.

32526222 10499112 02.08.2016 1/7



The range of the system can be optimised by selecting the optimal installation location, taking into account the structural circumstances.




Figure 2: Reduced range due to structural obstacles

Example of penetration of various materials:

Material	Penetration
Wood, Plaster, Plasterboard	approx. 90%
Brick, Chipboard	approx. 70%
Reinforced concrete	approx. 30%
Metal, Metal grid	approx. 10%
Rain, Snow	approx. 1-40%

Intended use

- Radio transmitter for transmission of switching, dimming, blind movement and light scene commands
- Operation via push-button sensors
- Installation in appliance box to DIN 49073 or in surface-mounted housing
- Operation with suitable radio actuators

Product characteristics

- Number of radio channels dependent on pushbutton used
- Each two opposite buttons belong to one channel
- Functions can be set with 4gang function switch Special functions "All Off" or "Light scene" can be assigned to individual buttons
- Battery-powered device

10499112 02.08.2016 2/7 32526222



4 Operation

Channel assignment of the push-button sensors




Figure 3: Channel assignment

Sending radio telegrams

Channel-Button, e.g. Press 1+ to transmit a radio telegram.
 The corresponding red LED lights up as an acknowledgement.

As long as no light scene functions were selected, the following responses occur, depending on the type of receiver:

Button	Length	Lighting	Venetian blind
X+	less than 1 second	Switch on	Slat adjustment
Х-	less than 1 second	Switch off	Slat adjustment
X+	longer than 1 second	brighter	blind moves up
X-	longer than 1 second	darker	blind moves down

- i The maximum transmitting length is 12 seconds, even if another button is pressed after that.
- i If more than one button is pressed at the same time, no radio telegram is transmitted.

Calling up light scenes

Light scene button has been taught (see Commissioning).

Press the light scene button for shorter than 3 seconds.
 Receivers switch to the stored light scene value.

Save light scene

Light scene button has been taught (see Commissioning).

- Set the required lighting situation.
- Press the light scene button for longer than 3 seconds.

First the old light scene is called up; do not release the button during this. After about 3 seconds the new light scene is saved and activated.

i If during saving of a light scene the blind is not in an end position, or is on the way there, then that blind is not integrated into the light scene.

32526222 10499112 02.08.2016 **3/7**



Call up All Off

In the teaching procedure for a channel button or a light scene button, the All Off button of the receiver is automatically also taught, with the exception of radio blind actuators.

Function switch 2 is in the **OFF** position (see Commissioning).

Press button 1- longer than 1 second
 The loads at all taught receivers are switched off.

5 Information for electrically skilled persons

5.1 Fitting and electrical connection

Connecting and mounting the device




Figure 4

Maintain a distance of at least 1 m between transmitter and receiver.

Maintain distance from large-area metal objects, e.g. metallic door frames.

- i Perform commissioning and teaching procedures before installation (see Commissioning).
- Install transmitter with screws in an appliance box or in a surface-mounted housing; the marking **TOP** must be at the top.
- i Lay the antenna (5) stretched out freely if possible and as far as possible from the transmitter.
- Inset batteries if necessary (see section Changing the batteries).
- Set function (see Commissioning).
- i The set function can be changed at any time.
- Install pushbutton (7) with frame (6).

Changing the batteries



WARNING!

Risk of chemical burns.

Batteries can burst and leak.

Exchange all batteries in a set at the same time.

Replace batteries only with an identical or equivalent type.

- Pull off pushbutton.
- Move function switch Batt. (3) to the left to the OFF position.

32526222 10499112 02.08.2016 4/7



- Open battery compartment (2) by turning anticlockwise.
- Remove empty batteries.




Figure 5

- i Keep contacts of batteries and device free of grease.
- Insert new batteries (8).
- Close battery compartment.
- Move function switch **Batt.** (3) to the right to the **ON** position.
- Press any button for approx. 1 second.
- Install pushbutton (7) with frame (6).
- To preserve the batteries, switch the transmitter off if no pushbutton is attached for a longer period. To do this, move function switch **Batt.** to the left to the **OFF** position.

5.2 Commissioning

Setting functions

The pushbutton is pulled off of the wall transmitter.

- Move **Batt.** switch (3) to the right to the **ON** position.
- Select functions of the buttons with the function switches (3) according to the following table (Figure 1).
- i The factory setting is shown in bold lettering.

Function switch	Button	OFF, left	ON, right
1	-	Batt. OFF	Batt. ON
2	Button 1- Button 1+	All Off Light scene 1	Channel 1- Channel 1+
3	Button 2- Button 2+	Light scene 2 Light scene 3	Channel 2+
4	Button 3- Button 3+	Light scene 4 Light scene 5	Channel 3+

i The buttons **4+** and **4-** always correspond to the channels **4+** and **4-**.

32526222 10499112 02.08.2016 5/7



- Attach frame and pushbutton
- Press any button for approx. 1 second.

Teaching transmitter in radio receiver

In order for a receiver to understand a radio telegram from the transmitter, the receiver has to "learn" this radio telegram. A channel of the transmitter can be taught in any number of receivers. The teaching procedure only results in an assignment in the receiver.

When teaching a transmitter, the range of the receiver is reduced to about 5 m. The distance between the receiver and the transmitter being taught should therefore be between 0.5 m and 5 m.

The function switch for the channel being taught is set to **ON**

- Switch radio receiver to programming mode (see instructions for receiver).
- Press the "+" or "-" button of the desired channel longer than 1 second.
- Exit programming mode of the receiver (see instructions for the receiver).
 The channel of the transmitter has now been taught in the radio receiver.

Teaching a light scene button

The function switch for button being taught is set to **OFF**.

- Switch receiver to programming mode (see instructions for receiver).
- Press the light scene button for longer than 3 seconds.
- Exit programming mode of the receiver (see instructions for the receiver).
 Light scene button has been taught.

Deleting All Off

If a certain receiver should not respond to the All Off button, then this function has to be deleted.

- Switch receiver to programming mode (see instructions for receiver).
- Press All Off button 1- for longer than 10 seconds.
 Function has been deleted.
- Exit programming mode of the receiver (see instructions for the receiver).

6 Appendix



Remove empty batteries immediately and dispose of in an environmentally friendly manner. Do not throw batteries into household waste. Consult your local authorities about environmentally friendly disposal. According to statutory provisions, the end consumer is obligated to return used batteries.

6.1 Technical data

Rated voltage
Battery type
Ambient temperature
Relative humidity
Radio frequency
Transmitting range in free field
Transmission capacity

DC 6 V 2×lithium CR 2032 0 ... +55 °C max. 80 % (No moisture condensation) 433.05 MHz ... 434.79 MHz typ. 100 m < 10 mW

6.2 Troubleshooting

After a brief button-press all LEDs flash 5 times.

Cause: batteries in wall transmitter are almost empty.

Change batteries (see section Changing the batteries).

32526222 10499112 02.08.2016 6/7



Receiver does not respond or only responds sometimes, but all LEDs light up when button is pressed.

Cause 1: Radio range exceeded. Structural obstacles reduce the range.

Check routing of antenna. Laying the antenna stretched out increases the range.

Using a radio repeater.

Cause 2: function switches are in the wront position.

Check positions of function switches.

6.3 Conformity

Gira Giersiepen GmbH & Co. KG hereby declares that the radio system type Order No. 0511 00

corresponds to the directive 2014/53/EU. You can find the full article number on the device. The complete text of the EU Declaration of Conformity is available under the Internet address: www.gira.de/konformitaet

6.4 Warranty

The warranty follows about the specialty store in between the legal framework as provided for by law

Please submit or send faulty devices postage paid together with an error description to your responsible salesperson (specialist trade/installation company/electrical specialist trade). They will forward the devices to the Gira Service Center.

Gira

Giersiepen GmbH & Co. KG Elektro-Installations-Systeme

Industriegebiet Mermbach Dahlienstraße 42477 Radevormwald

Postfach 12 20 42461 Radevormwald

Deutschland

Tel +49(0)21 95 - 602-0 Fax +49(0)21 95 - 602-191

www.gira.de info@gira.de

32526222 10499112 02.08.2016 7/7