




Best. Nr.			 LED			
	n	W	n	W	n	W
2015 00	5	280	2	200	4	280
2025 00	5	280	2	200	4	280
2171 00 abV04	2	420	2	200	2	420
2172 00 abV04	4	420	2	200	4	420
2174 00 abV04	4	420	2	200	4	420
2365 00	5	420	2	200	5	420
2385 00	5	420	2	200	5	420
2440 00	2	210	2	200	2	210
2450 00	5	210	2	200	5	210
2455 00	5	420	2	200	5	420
5400 00	5	210	2	200	5	210
5401 00	5	420	2	200	5	420
5402 00	3	350	2	200	3	350
5420 00	5	250	2	200	5	250
5430 00	3	420	2	200	3	420
5431 00	4	420	2	200	4	420

Figure 4: Trailing edge phase control





Best. Nr.			 LED					
	n	W	n	W	n	W	n	VA
2015 00	2	350	2	50	4	280	2	380
2025 00	2	350	2	50	4	280	2	380
2171 00 abV04	2	420	2	100	2	420	2	420
2172 00 abV04	4	420	2	100	4	420	4	420
2174 00 abV04	4	420	2	100	4	420	4	420
2365 00	5	420	2	100	5	420	5	420
2385 00	5	420	--	--	5	420	5	420
2440 00	2	210	2	50	2	210	2	210
2450 00	5	210	2	60	5	210	5	210
2455 00	5	420	2	100	5	420	5	420
5400 00	5	210	2	60	5	210	5	210
5401 00	5	420	2	100	5	420	5	420
5402 00	3	350	2	100	3	350	3	350
5420 00	5	250	2	70	5	250	5	250
5430 00	3	420	2	65	3	420	3	420
5431 00	4	420	2	100	4	420	4	420

Figure 5: Leading edge phase control

Minimum load for combination of dimmer with one power booster

Not LED loads

200 W / VA

LED loads leading edge phase control

75 W

LED loads trailing edge phase control

200 W